

How to Order Die-Cut CHO-THERM® Insulators

Standard die-cut parts are ordered using the following Part Number System.






For custom parts contact Chomerics.

WW
60 = Standard die-cut part








XX
11 = No PSA
12 = PSA one side

YYYY
Standard Configuration Drawing Number







ZZZZ
CHO-THERM® Material
Example: 1671, T500, etc.

RECOMMENDED SCREW/TORQUE	CONFIGURATION	DIMENSIONS (INCHES)									ORDERING NUMBER PART NUMBER	
		A	B	C	D	E	F	G	H	I		
#4-40 5 in-lb #6-32 6 in-lb	T0-3 	1.563	1.050	.140	.080							WW-XX-D065-ZZZZ
		1.563	1.050	.140	.140							WW-XX-4305-ZZZZ
		1.593	1.100	.156	.070							WW-XX-4511-ZZZZ
		1.650	1.065	.140	.046							WW-XX-D370-ZZZZ
		1.650	1.140	.122	.062							WW-XX-D371-ZZZZ
		1.650	1.140	.140	.093							WW-XX-6875-ZZZZ
		1.650	1.140	.165	.062							WW-XX-D372-ZZZZ
		1.650	1.140	.140	.046							WW-XX-D373-ZZZZ
		1.650	1.140	.165	—							WW-XX-D374-ZZZZ
		1.700	1.187	.156	.062							WW-XX-4996-ZZZZ
		1.730	1.250	.156	.062							WW-XX-5442-ZZZZ
		1.780	1.250	.140	.093							WW-XX-D375-ZZZZ
		1.780	1.250	.165	.094							WW-XX-D376-ZZZZ
		1.780	1.250	.140	.046							WW-XX-D377-ZZZZ
2.07	1.56	.122	.062							WW-XX-D378-ZZZZ		
#4-40 5 in-lb #6-32 6 in-lb	3 LEAD T0-3 	1.65	1.140	.140	.093	1.187	.430				WW-XX-D379-ZZZZ	
#4-40 5 in-lb #6-32 6 in-lb	4 LEAD T0-3 	1.560	1.050	.158	.080	1.170					WW-XX-D380-ZZZZ	
		1.563	1.050	.156	.063	1.187					WW-XX-D381-ZZZZ	
#4-40 5 in-lb #6-32 6 in-lb	8 LEAD T0-3 	1.655	1.187	.156	.060						WW-XX-D382-ZZZZ	
#4-40 5 in-lb #6-32 6 in-lb	10 LEAD T0-3 	1.650	1.140	.165	.040						WW-XX-D383-ZZZZ	

(1 in-lb = 1.152 kg-cm)

RECOMMENDED SCREW/TORQUE	CONFIGURATION	DIMENSIONS (INCHES)									ORDERING NUMBER PART NUMBER
		A	B	C	D	E	F	G	H	I	
#4-40 3 in-lb #6-32 4 in-lb	TO-66 	1.250	.700	.140	.062						WW-XX-4353-ZZZZ WW-XX-5527-ZZZZ WW-XX-4997-ZZZZ WW-XX-D384-ZZZZ
		1.312	.762	.140	.062						
		1.375	.825	.140	.062						
		1.440	1.000	.140	.075						
#4-40 3 in-lb #6-32 4 in-lb	3 LEAD TO-66 	1.275	.750	.156	.100	.960					WW-XX-D385-ZZZZ
#4-40 3 in-lb #6-32 4 in-lb	4 LEAD TO-66 	1.312	.762	.140	.062	.960	.200	.100			WW-XX-D386-ZZZZ
#4-40 3 in-lb #6-32 4 in-lb	9 LEAD TO-66 	1.440	1.000	.140	.055	.960	.480	.325			WW-XX-D387-ZZZZ
#4-40 3 in-lb #6-32 4 in-lb	MULTI LEAD TO-66 	1.35	.800	.140	.400						WW-XX-D388-ZZZZ
#4-40 2 in-lb	TO-220 	.437	.312	.140	.093						WW-XX-D389-ZZZZ WW-XX-D390-ZZZZ WW-XX-D391-ZZZZ WW-XX-D392-ZZZZ WW-XX-5791-ZZZZ WW-XX-8302-ZZZZ WW-XX-D393-ZZZZ WW-XX-8531-ZZZZ WW-XX-6956-ZZZZ WW-XX-D394-ZZZZ WW-XX-D395-ZZZZ WW-XX-D396-ZZZZ WW-XX-D397-ZZZZ WW-XX-D398-ZZZZ WW-XX-D399-ZZZZ WW-XX-D400-ZZZZ WW-XX-D401-ZZZZ
		.437	.312	.140	.122						
		.500	.385	.170	.120						
		.610	.560	.245	.125						
		.687	.562	.218	.125						
		.710	.500	.160	.141						
		.750	.410	.225	.156						
		.750	.500	—	—						
		.750	.500	.187	.147						
		.750	.500	.187	.125						
		.750	.600	.240	.150						
		.750	.600	.240	.115						
		.855	.562	.218	.125						
		.855	.630	.230	.093						
		.860	.740	.200	.160						
		1.125	.625	.200	.145						
1.410	.810	.355	.147								
#4-40 2 in-lb		.910	.500	.200	.125	.580	.046	.265			WW-XX-D402-ZZZZ WW-XX-D403-ZZZZ
		.983	.750	.432	.156	.665	.101	.217			

(1 in-lb = 1.152 kg-cm)

RECOMMENDED SCREW/TORQUE	CONFIGURATION	DIMENSIONS (INCHES)									ORDERING NUMBER PART NUMBER	
		A	B	C	D	E	F	G	H	I		
#4-40 2 in-lb	TYPE II TO-220 	1.00	.500	.200	.141	.626						WW-XX-4969-ZZZZ
#10-32 2 in-lb #25-28 7 in-lb	DIODE WASHERS DO-4  DO-5	.360 .510 .510 .512 .625	.260 .140 .200 .161 .195									WW-XX-D404-ZZZZ WW-XX-D405-ZZZZ WW-XX-D406-ZZZZ WW-XX-D407-ZZZZ WW-XX-4659-ZZZZ WW-XX-D408-ZZZZ WW-XX-D409-ZZZZ WW-XX-D410-ZZZZ WW-XX-D411-ZZZZ WW-XX-D412-ZZZZ WW-XX-D413-ZZZZ WW-XX-D414-ZZZZ WW-XX-4661-ZZZZ WW-XX-D415-ZZZZ WW-XX-D416-ZZZZ WW-XX-D417-ZZZZ WW-XX-D418-ZZZZ
	TO-36 	1.063	.690	.200							WW-XX-4306-ZZZZ	
	TO-5 and TO-18 3 holes  4 holes	.250 .360 .390	.100 .200 .200	.036 .040 .040							WW-XX-D419-ZZZZ WW-XX-4374-ZZZZ WW-XX-D420-ZZZZ WW-XX-D421-ZZZZ WW-XX-D422-ZZZZ WW-XX-D423-ZZZZ	
#4-40 2 in-lb	RECTIFIER 	.100 1.125 1.250	.100 1.125 1.250	.187 .140 .200							WW-XX-D424-ZZZZ WW-XX-D425-ZZZZ WW-XX-D426-ZZZZ	
#4-40 2 in-lb	TIP PACKAGE 	.865 .865 .984 .984 1.260	.650 .650 .787 .787 .787	.650 .650 — .708 .984	.140 .140 — .142 .142						WW-XX-5792-ZZZZ WW-XX-D427-ZZZZ WW-XX-D428-ZZZZ WW-XX-D429-ZZZZ WW-XX-D430-ZZZZ	

(1 in-lb = 1.152 kg-cm)