


RF Absorber Material UL94 VO Rated

DESCRIPTION


CHO-MUTE™ 9025 elastomer RF absorber is designed to offer wide band attenuation within operating frequencies of 30MHz to 12 GHz. Typical electronics systems operating within this band are personal computers, mobile phones and PDA's. CHO-MUTE 9025 incorporates a high tech silicone polymer system that offers the benefit of wide band absorption and high permeability in a lightweight and flexible product form. CHO-MUTE 9025 is extremely effective in absorbing surface currents along with free space electromagnetic fields.

BENEFITS

- RF absorption material covering a wide range of frequency.
 - CHO-MUTE 9025 Material "30MHz to 12GHz"
- High performance RF absorption - Up to 20 dB
- Available in several thicknesses:
 - 0.010" (0.25mm) through 0.125" (3.2mm)
- Flexible
- UL94 VO Flame Rated (0.25mm through 3.2mm)
- RoHS Compliant
- Global product availability



Typical Application



RF ABSORPTION

CHO-MUTE 9025 material exhibits high permeability and magnetic loss tangents. CHO-MUTE 9025 material is an excellent cavity resonant absorber and provides broadband free space absorption from 30MHz to 12GHz.

APPLICATIONS



CHO-MUTE 9025 material can be used on a variety of applications to eliminate problems EMI/EMC problems in, transmitters, transceivers, microcontrollers, microprocessors etc.

Potential applications include:

- Hand held electronics, wireless voice or data telecommunication, infotainment, testing equipment, PDAs
- Military electronics, C3I, navigation, GPS, ruggedized computers, night vision
- Antenna performance, surface current reduction
- Office and telecommunication infrastructure equipment, computing, switch gear, power amplifiers, and routers.

AVAILABILITY

CHO-MUTE 9025 material is available globally in sheets, die cut or molded parts. Sheets are available with or without PSA and the thickness ranging from 0.01" (0.25mm) to 0.125" (3.0mm).



Standard Sheet Stock Part Number


46-**TA**-1020-9025

Thickness, inch (mm) **A**dhesive (PSA)

- | | | | |
|----|--------------|----|------------------|
| 1. | 0.020 (0.51) | 0. | No Adhesive |
| 2. | 0.032 (0.81) | 1. | Adhesive Backing |
| 3. | 0.062 (1.57) | | |
| 4. | 0.093 (2.36) | | |
| 5. | 0.125 (3.18) | | |
| 7. | 0.010 (0.25) | | |

Custom shapes available. Contact Parker Chomerics for quote
Standard sheet dimension is 10" (25.4cm) x 20" (50.8cm)

dB/cm Absorption



Typical Properties		
Property	Units	CHO-MUTE 9025
COMPOSITION		
Ferrous filled silicone		
ELECTRICAL		
Surface Resistance Initial	Ω/square	>1M
Bulk Volume Resistivity Initial	Ω•cm	>1M
MECHANICAL		
Operating Temperature Range		-50°C to 160°C
Tensile Strength	PSI (MPa)	500 (3.44)
Elongation	(% min)	200
Hardness "Shore A"	Shore A	55
Tear Strength	Lb/in (N/m)	60 (10.5k)
THERMAL		
Thermal Conductivity	W/m-K	0.87
PHYSICAL		
Specific Gravity		3.4

CHOMERICS is a registered trademark of Parker Hannifin Corporation. CHO-MUTE is a trademark of Parker Hannifin Corporation. © Copyright 2006 Parker Hannifin Corporation. All rights reserved.

TB 1039 EN 8/08

www.chomerics.com

North America • 77 Dragon Court, Woburn, MA 01888-4014 TEL +(1) 781-935-4850 FAX +(1) 781-933-4318
 Europe • Marlow, Bucks, UK TEL +(44) 1628 404000 FAX +(44) 1628 404090
 Asia Pacific • Hong Kong TEL +(852) 2 428 8008 FAX +(852) 2 423 8253
 South America • São Paulo, Brazil TEL +(55) 11 3917 1099 FAX +(55) 11 3917 0817



⚠ WARNING – USER RESPONSIBILITY

FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

OFFER OF SALE

The items described in this document are hereby offered for sale by Parker-Hannifin Corporation, its subsidiaries or its authorized distributors. This offer and its acceptance are governed by the provisions stated in the detailed "Offer of Sale" elsewhere in this document or available at: <http://www.chomerics.com/salesterms>