

MATERIAL SAFETY DATA SHEET

**CHOMERICS DIVISION
PARKER HANNIFIN CORPORATION
77 DRAGON COURT
WOBURN, MA 01888
TEL: 781-935-4850**

SECTION 1 PRODUCT IDENTIFICATION

Product Name: **CHO-BOND 584**
General Chemical Description: Conductive Epoxy

SECTION 2 COMPOSITION INFORMATION

<u>Components & CAS. No.</u>	<u>Weight %</u>	<u>Exposure Limits</u>
Silver 7440-22-4	65 - 75	OSHA PEL TWA: 0.01 mg/m ³ ; ACGIH TLV TWA: 0.1 mg/m ³ .
Epoxy Resin 25068-38-6	20 - 30	Not Established
o-Cresyl glycidyl ether 2210-79-9	<10	Not Established

SECTION 3 HAZARDS IDENTIFICATION

Emergency Overview: Silver liquid with a mild odor. May cause severe irritation of eyes and skin as well as skin sensitization. May cause irritation of mucous membranes and respiratory tract. Chronic health hazards. Refer to other sections of the MSDS for more detailed information.

HMIS Rating: Health: 3 Flammability: 1 Reactivity: 0

Routes of Entry: Inhalation, skin and eye contact.

Acute Effects:

Eye: Contact may cause severe eye irritation.

Skin: Contact may cause severe skin irritation. Contact may cause sensitization, an allergic skin reaction, with symptoms including reddening, swelling, rash, scaling or blistering. Persons sensitized may exhibit these symptoms on subsequent contact with very small amounts of material or as a result of exposure to vapor.

Inhalation: This product contains o-cresyl glycidyl ether that upon inhalation may cause irritation of mucous membranes and respiratory tract and central nervous system depression.

Ingestion: Harmful if swallowed.

Chronic Effects: Prolonged or repeated contact with silver may result in argyria, a blue-gray discoloration of the eyes, skin or other body tissue. Once deposited, there is no known means by which the silver can be eliminated; the pigmentation is permanent.

o-Cresyl glycidyl ether has been reported to be mutagenic in in-vitro tests.

Special Condition Effects: Not applicable.

Aggravated Medical Conditions: No data is available for this product mixture.

SECTION 4 FIRST AID MEASURES:

Handle in accordance with good industrial hygiene and safety practices by avoiding unnecessary exposure and by removing material from the eyes, skin and clothing.

Eye: Immediately and gently flush the eyes with large amounts of water for at least 15 minutes, occasionally lifting the upper and lower eyelids. Get medical attention.

Skin: Remove contaminated clothing. Thoroughly wash skin with soap and water for at least 15 minutes. Get immediate medical attention if irritation persists or if symptoms of exposure develop (see SECTION 3 - HAZARDS IDENTIFICATION).

Inhalation: Remove to fresh air. Get immediate medical attention if irritation persists, breathing becomes difficult or if symptoms (as described in SECTION 3) develop.

Ingestion: Get medical attention. Never give anything by mouth to an unconscious, drowsy or convulsing person.

SECTION 5 FIRE FIGHTING MEASURES

Flash Point: Not Established. >200°F

Autoignition Temp.: Not Established.

Flammable Limits: Not Established

Extinguishing Media: Carbon dioxide, water, water foam, dry chemical.

Fire Fighting Procedures: Use self-contained breathing apparatus and protective clothing. If large quantities of material are involved, evacuate area and fight fire from a safe distance.

Unusual Fire Hazards: Decomposition and combustion products may be toxic.

SECTION 6 ACCIDENTAL RELEASE MEASURES

Spill response operations must be conducted in accordance with the provisions of 29 CFR 1910.120. Observe all recommendations identified in Sections 5 and 8.

Procedures: Limit access to spill area. Dike area to contain the release. Prevent release from entering sewers or waterways. Collect spill materials for reuse or salvage. Cover remaining spilled materials with inert material to absorb residue. Transfer liquids and absorbed materials to appropriate containers. Observe all applicable local, state and federal waste management regulations.

SECTION 7 HANDLING AND STORAGE

Handling: Do not allow contact with eyes. Do not allow skin contact. Avoid exposure by inhalation. Wash thoroughly after handling and before eating, drinking or smoking. Use with adequate ventilation.

Storage: Store in a cool dry location with adequate ventilation. Store in tightly closed container. Keep away from open flame and heat sources. Prevent contact and storage with incompatible materials.

SECTION 8 EXPOSURE CONTROLS/PERSONAL PROTECTION

The recommendations described in this section are provided as general guidance for minimizing exposure. Because usage conditions vary with customer applications, specific exposure controls should be developed by a person knowledgeable in the intended usage condition and equipment.

Ventilation: Local exhaust ventilation should not be required at room temperature. However, when the product is processed at elevated temperatures, provide local exhaust ventilation to capture vapors, mists or fumes generated. Ventilation must be sufficient to maintain airborne levels of Section 2 ingredients below their exposure limits.

Eyes: Wear safety eye wear including safety glasses with side shields and chemical goggles if splashing may occur.

Skin: Wear protective gloves to minimize skin contact. Wash thoroughly after handling and before eating, drinking or smoking. Remove contaminated clothing or shoes and thoroughly clean before reuse.

Inhalation: No respiratory protection should be required. However, use NIOSH/MSHA approved respiratory protection if adequate exhaust ventilation is not provided or air sampling indicates exposure limits are exceeded. The type of respirator selected will depend on the condition of use. Respiratory protection programs must comply with 29 CFR 1910.134.

SECTION 9 PHYSICAL AND CHEMICAL PROPERTIES

Physical Form: Silver liquid.
Specific Gravity: >1
Boiling Point : Not Established.
Vapor Pressure (25°C): Not Established.
Vapor Density: Not Established.
Solubility in Water: Insoluble.
Volatile Content (Wt%): Not Established.

SECTION 10 STABILITY AND REACTIVITY

Chemical Stability: Stable.
Hazardous Polymerization: Will not occur.
Condition to Avoid: Avoid storage in open containers, exposure to open flame or exposure to incompatible substances.
Incompatibilities: Strong oxidizers, acids, bases, amines and mercaptans.
Hazardous Decomposition: Thermal or chemical decomposition may produce carbon monoxide, carbon dioxide, silver compounds, and traces of incompletely burned carbon products.

SECTION 11 TOXICOLOGY INFORMATION

All available toxicology information has been provided in Section 3 of this document.

SECTION 12 ECOLOGICAL INFORMATION

No data on ecological effects is available.

SECTION 13 DISPOSAL INFORMATION

Since regulations vary, consult applicable regulations or authorities before disposing of this material.

SECTION 14 TRANSPORTATION INFORMATION

This product is not regulated as a hazardous material by the U.S. Department of Transportation.

SECTION 15 REGULATORY AND MISCELLANEOUS INFORMATION

TSCA: All components of this product are listed on the TSCA inventory.

SARA 313 Chemicals: Silver 7440-22-4

Date Prepared: 3-9-2007
Document Number: 584
Supersedes: 6-22-1999
Prepared By: Chomerics Safety Department

Revision Information: HMIS Rating added. Section 11, 12, 13 updated.

This information and recommendations herein are based upon data considered true and accurate. However, Chomerics makes no warranties, express or implied as to the accuracy or adequacy of the information contained herein or the results to be obtained from the use thereof. This information is offered solely for the user's consideration, investigation and verification. Since the use and conditions of use of this information and material are not within the control of Chomerics, Chomerics assumes no responsibility for injury to the user or third persons. The material described herein is sold pursuant to Chomerics' Terms and Conditions of Sale, including those limiting warranties and remedies contained therein. It is the responsibility of the user to determine whether any use of this data and information is in accordance with applicable federal, state or local laws and regulations.