

Extrusion Product Guide

Custom Extrusions

Custom Extrusion Capabilities


As the world's leading supplier of conductive elastomer gaskets, Chomerics routinely supports its customers by producing extruded gaskets in special configurations. These range from unusual sizes in

standard shapes to highly complex designs that meet specialized shielding and environmental sealing requirements.

The following "showcase" includes representative examples of our custom extrusion capabilities. If you are interested in adapting one of

these shapes to your design, or developing an altogether new gasket design, contact our Applications Engineering Department. We welcome the opportunity to assist you.

Custom A Profiles



Dimensions shown in inches; 1 in. = 25.4 mm

Custom D Profiles

<p>10-05-10648-XXXX</p>	<p>10-05-14081-XXXX</p>	<p>19-09-14757-XXXX</p>	<p>19-09-19925-XXXX</p>
<p>19-09-19926-XXXX</p>	<p>10-5-3369-XXXX</p>	<p>10-05-4318-XXXX</p>	<p>10-05-8635-XXXX</p>
<p>19-05-B248-XXXX</p>	<p>19-05-B250-XXXX</p>	<p>19-05-B254-XXXX</p>	<p>19-05-B363-XXXX</p>
<p>19-09-L547-XXXX</p>	<p>19-09-23271-XXXX</p>	<p>19-09-22965-XXXX</p>	<p>19-09-23309-XXXX</p>
<p>19-09-23709-XXXX</p>	<p>10-05-4035-XXXX</p>		

Custom P Profiles

<p>19-06-11400-XXXX</p>	<p>19-09-19944-XXXX</p>	<p>19-09-20733-XXXX</p>	<p>19-09-21275-XXXX</p>
<p>19-09-LA06-XXXX</p>	<p>19-09-22539-XXXX</p>		

Dimensions shown in inches; 1 in. = 25.4 mm

Custom Ribbed Profiles

<p>19-09-10921-XXXX</p>	<p>10-09-11118-XXXX</p>	<p>19-09-11370-XXXX</p>	<p>19-09-11411-XXXX</p>
<p>19-09-11859-XXXX</p>	<p>19-09-13072-XXXX</p>	<p>19-09-23139-XXXX</p>	<p>19-09-24767-XXXX</p>

Custom Hat Profiles

<p>19-09-11367-XXXX</p>	<p>19-09-11408-XXXX</p>	<p>19-09-11409-XXXX</p>	<p>19-09-11641-XXXX</p>
<p>19-09-11883-XXXX</p>	<p>19-09-12012-XXXX</p>	<p>19-09-17438-XXXX</p>	<p>19-09-21618-XXXX</p>

Dimensions shown in inches; 1 in. = 25.4 mm

Custom Mushroom Profiles

<p>19-05-14282-XXXX</p>	<p>19-09-14377-XXXX</p> <p>U.S. Patent No. 06075205</p>	<p>19-05-14587-XXXX</p> <p>U.S. Patent No. 06075205</p>	<p>19-09-14926-XXXX</p> <p>U.S. Patent No. 06075205</p>
<p>19-09-15486-XXXX</p> <p>U.S. Patent No. 06075205</p>	<p>19-09-15523-XXXX</p> <p>U.S. Patent No. 06075205</p>	<p>19-09-16339-XXXX</p>	<p>19-09-16503-XXXX</p> <p>U.S. Patent No. 06075205</p>
<p>19-09-16802-XXXX</p> <p>U.S. Patent No. 06075205</p>			


Custom Profiles

<p>19-09-10357-XXXX</p>	<p>19-09-10843-XXXX</p>	<p>19-08-10873-XXXX</p>	<p>19-09-11219-XXXX</p>
<p>19-09-11225-XXXX</p>	<p>19-08-11240-XXXX</p>	<p>19-09-11401-XXXX</p>	<p>19-09-11434-XXXX</p>
<p>19-09-11735-XXXX</p>	<p>19-09-11755-XXXX</p>	<p>19-09-11860-XXXX</p>	<p>19-09-12389-XXXX</p>
<p>19-09-12756-XXXX</p>	<p>19-08-12876-XXXX</p>	<p>19-09-13225-XXXX</p>	<p>19-09-13569-XXXX</p>

Dimensions shown in inches; 1 in. = 25.4 mm

<p>19-09-13851-XXXX</p>	<p>19-09-14182-XXXX</p>	<p>19-09-14350-XXXX</p>	<p>19-09-14645-XXXX</p>
<p>19-09-14831-XXXX</p>	<p>19-05-15097-XXXX</p>	<p>19-09-15111-XXXX</p>	<p>19-09-15142-XXXX</p>
<p>19-09-15245-XXXX</p>	<p>19-09-15377-XXXX</p>	<p>19-09-15562-XXXX</p>	<p>19-09-15786-XXXX</p>
<p>10-09-15862-XXXX</p>	<p>19-09-15904-XXXX</p>	<p>19-08-15937-XXXX</p>	<p>19-09-16078-XXXX</p>
<p>19-09-16336-XXXX</p>	<p>19-09-16623-XXXX</p>	<p>19-09-16891-XXXX</p>	<p>19-09-16961-XXXX</p>
<p>19-24-16966-XXXX</p>	<p>19-09-17276-XXXX</p>	<p>19-09-17428-XXXX</p>	<p>19-09-17429-XXXX</p>
<p>19-09-18963-XXXX</p>	<p>19-09-19022-XXXX</p>	<p>19-09-19234-XXXX</p>	<p>19-18-19561-XXXX</p>

Dimensions shown in inches; 1 in. = 25.4 mm



Dimensions shown in inches; 1 in. = 25.4 mm

<p>19-09-LE24-XXXX</p>	<p>19-09-LF15-XXXX</p>	<p>19-09-LF60-XXXX</p>	<p>19-09-LF69-XXXX</p>
<p>19-09-LG41-XXXX</p>	<p>19-09-W068-XXXX</p>	<p>19-09-W321-XXXX</p>	<p>19-09-W949-XXXX</p>
<p>10-09-10824-XXXX</p>	<p>19-09-21467-XXXX</p>	<p>19-09-21862-XXXX</p>	<p>19-09-22079-XXXX</p>
<p>19-09-22103-XXXX</p>	<p>19-09-23266-XXXX</p>	<p>19-09-23351-XXXX</p>	<p>19-09-23456-XXXX</p>
<p>19-08-23630-XXXX</p>	<p>19-09-23686-XXXX</p>	<p>19-09-24443-XXXX</p>	<p>19-09-24559-XXXX</p>

Dimensions shown in inches; 1 in. = 25.4 mm