

Custom Extrusions

Custom Extrusion Capabilities

As the world's leading supplier of conductive elastomer gaskets, Chomerics routinely supports its customers by producing extruded gaskets in special configurations. These

range from unusual sizes in standard shapes to highly complex designs that meet specialized shielding and environmental sealing requirements.

The following "showcase" includes representative examples of our custom extrusion capabilities. If you are

interested in adapting one of these shapes to your design, or developing an altogether new gasket design, contact our Applications Engineering Department. We welcome the opportunity to assist you.

<p>19-09-LF15-XXXX</p>	<p>19-09-10076-XXXX</p>	<p>19-09-10645-XXXX</p>	<p>19-09-11540-XXXX</p>
<p>19-09-13233-XXXX</p>	<p>19-09-9325-XXXX</p>	<p>19-09-C830-XXXX</p>	<p>19-09-E053-XXXX</p>
<p>19-09-E620-XXXX</p>	<p>19-09-F948-XXXX</p>	<p>19-09-L913-XXXX</p>	<p>19-09-14446-XXXX</p>
<p>19-09-M942-XXXX</p>	<p>19-09-X962-XXXX</p>	<p>19-09-M530-XXXX</p>	<p>19-09-11860-XXXX</p>
<p>19-09-10053-XXXX</p>	<p>19-08-10873-XXXX</p>	<p>19-08-11236-XXXX</p>	<p>19-08-11240-XXXX</p>

Dimensions shown in inches; 1 in. = 25.4 mm

<p>19-09-12023-XXXX</p>	<p>19-08-12057-XXXX</p>	<p>19-08-12876-XXXX</p>	<p>19-09-13209-XXXX</p>
<p>19-09-13456-XXXX</p>	<p>19-09-13835-XXXX</p>	<p>10-08-8754-XXXX</p>	<p>19-08-C127-XXXX</p>
<p>19-09-C369-XXXX</p>	<p>19-09-F534-XXXX</p>	<p>19-09-LA06-XXXX</p>	<p>19-09-LF59-XXXX</p>
<p>19-09-W795-XXXX</p>	<p>19-08-W805-XXXX</p>	<p>19-08-X175-XXXX</p>	<p>19-08-X179-XXXX</p>
<p>19-08-Z724-XXXX</p>	<p>19-09-15097-XXXX</p>	<p>19-09-W068-XXXX</p>	<p>19-09-12756-XXXX</p>
<p>19-09-12841-XXXX</p>	<p>19-09-13225-XXXX</p>	<p>19-09-14182-XXXX</p>	<p>10-09-9420-XXXX</p>
<p>19-09-C832-XXXX</p>	<p>19-09-LB02-XXXX</p>	<p>19-09-M615-XXXX</p>	<p>19-09-M531-XXXX</p>

Dimensions shown in inches; 1 in. = 25.4 mm

continued

<p>19-09-A593-XXXX</p>	<p>19-09-LE24-XXXX</p>	<p>19-09-A846-XXXX</p>	<p>19-09-11409-XXXX</p>
<p>19-05-4535-XXXX</p>	<p>19-09-E368-XXXX</p>	<p>10-09-11408-XXXX</p>	<p>19-09-11883-XXXX</p>
<p>19-09-12012-XXXX</p>	<p>19-09-E367-XXXX</p>	<p>10-09-A614-XXXX</p>	<p>19-05-11558-XXXX</p>
<p>19-09-10280-XXXX</p>	<p>10-09-A469-XXXX</p>	<p>19-09-LD90-XXXX</p>	<p>19-09-LD89-XXXX</p>
<p>19-09-13569-XXXX</p>	<p>19-07-A251-XXXX</p>	<p>19-09-10921-XXXX</p>	<p>19-09-11118-XXXX</p>
<p>19-09-11859-XXXX</p>	<p>19-09-11370-XXXX</p>	<p>19-04-11411-XXXX</p>	<p>19-04-12336-XXXX</p>
<p>19-09-13072-XXXX</p>	<p>19-09-14377-XXXX</p> <p style="text-align: center;">U.S. Patent No.06075205</p>	<p>19-09-14587-XXXX</p> <p style="text-align: center;">U.S. Patent No.06075205</p>	<p>19-09-14926-XXXX</p> <p style="text-align: center;">U.S. Patent No.06075205</p>

Dimensions shown in inches; 1 in. = 25.4 mm

<p>19-09-15245-XXXX</p>	<p>19-09-15486-XXXX</p> <p>U.S. Patent No.06075205</p>	<p>19-09-15523-XXXX</p> <p>U.S. Patent No.06075205</p>	<p>19-09-15904-XXXX</p> <p>U.S. Patent No.06075205</p>
<p>19-09-15905-XXXX</p> <p>U.S. Patent No.06075205</p>	<p>19-09-16503-XXXX</p> <p>U.S. Patent No.06075205</p>	<p>19-09-16610-XXXX</p>	<p>19-09-16802-XXXX</p> <p>U.S. Patent No.06075205</p>
<p>19-07-10696-XXXX</p>	<p>19-09-10810-XXXX</p>	<p>19-09-11219-XXXX</p>	<p>19-09-11277-XXXX</p>
<p>19-09-A150-XXXX</p>	<p>19-09-C264-XXXX</p>	<p>19-09-F204-XXXX</p>	<p>19-08-F464-XXXX</p>
<p>19-09-LB05-XXXX</p>	<p>19-09-LB67-XXXX</p>	<p>19-09-LE14-XXXX</p>	<p>19-09-LG41-XXXX</p>
<p>19-09-LJ16-XXXX</p>	<p>19-09-W089-XXXX</p>	<p>10-09-W300-XXXX</p>	<p>19-09-W321-XXXX</p>
<p>10-09-W949-XXXX</p>	<p>19-09-Z730-XXXX</p>	<p>19-09-14350-XXXX</p>	<p>19-09-14351-XXXX</p>

Dimensions shown in inches; 1 in. = 25.4 mm

continued

<p>19-09-14831-XXXX</p>	<p>19-06-15027-XXXX</p>	<p>19-09-15142-XXXX</p>	<p>19-09-15464-XXXX</p>
<p>19-09-15551-XXXX</p>	<p>19-09-F158-XXXX</p>	<p>19-09-LF60-XXXX</p>	<p>19-09-LF69-XXXX</p>
<p>19-09-15377-XXXX</p>	<p>19-09-10809-XXXX</p>	<p>19-09-10843-XXXX</p>	<p>19-09-11225-XXXX</p>
<p>19-09-11346-XXXX</p>	<p>19-06-11400-XXXX</p>	<p>10-09-11434-XXXX</p>	<p>19-09-11530-XXXX</p>
<p>19-09-11755-XXXX</p>	<p>19-08-12643-XXXX</p>	<p>19-09-13045-XXXX</p>	<p>19-09-13392-XXXX</p>
<p>19-08-3492-XXXX</p>	<p>19-09-8222-XXXX</p>	<p>19-05-9514-XXXX</p>	<p>19-09-A240-XXXX</p>
<p>19-09-B363-XXXX</p>	<p>19-09-C032-XXXX</p>	<p>19-09-C428-XXXX</p>	<p>19-09-C628-XXXX</p>

Dimensions shown in inches; 1 in. = 25.4 mm

<p>19-05-E328-XXXX</p>	<p>19-08-F676-XXXX</p>	<p>19-09-W517-XXXX</p>	<p>19-09-X681-XXXX</p>
<p>19-06-11864-XXXX</p>	<p>19-09-13946-XXXX</p>	<p>19-06-14313-XXXX</p>	<p>19-09-15380-XXXX</p>
<p>19-09-15786-XXXX</p>	<p>19-09-16750-XXXX</p>	<p>19-07-W470-XXXX</p>	<p>19-09-13997-XXXX</p>
<p>19-09-15562-XXXX</p>	<p>19-09-15862-XXXX</p>	<p>19-09-15895-XXXX</p>	<p>19-09-15937-XXXX</p>
<p>19-09-16047-XXXX</p>	<p>19-09-16072-XXXX</p>	<p>19-09-16166-XXXX</p>	<p>19-09-16336-XXXX</p>
<p>19-06-L386-XXXX</p>	<p>19-09-10357-XXXX</p>	<p>19-09-11261-XXXX</p>	<p>19-09-12999-XXXX</p>
<p>19-09-11367-XXXX</p>	<p>19-09-11389-XXXX</p>	<p>19-09-11735-XXXX</p>	<p>19-06-13540-XXXX</p>

Dimensions shown in inches; 1 in. = 25.4 mm

continued

